
Mini-MD sample strike off machine


For the perfect printing sample prior to the printing production process you may opt for the Mini-MD sample strike off machine for flat screen and / or rotary screen printing.





Mini-MD-F flatscreen sample printing machine

Printing head fine adjustment





Mini-MD-R rotary screen sample printing machine

Screen washing machine

Mini-MD strike off-machine is available in size 60 x 70 cms or 60 x 128 cms. It may be used for the development and verification of paste viscosities, colour concentration and magnet power adjustments.

Rotary and squeegee device washing machines are available for either one, two, three or four screens at a time and up to six squeegees.





autumn 2015 www.zimmer-austria.com page 5 autumn 2015 www.zimmer-austria.com page 6 autumn 2015 www.zimmer-austria.com


| Midi-II unbatching device with infrared heater and wet glueing device.

Unbatching device



6 | Midi-II washing device with high quality rotating brush, drying squeegee and pneumatic lifting device.

Washing device



ZIMMER AUSTRIA | SCREEN & COATING SYSTEMS

The Midi-II-F flat screen printing system

is the most versatile flat screen sample printing machine on the market, suitable for all kinds of textile fabrics. The repeat length, the speed and the number of squeegee strokes as well as the magnetic power are individually adjustable on each printing station. Very fast set-up of screens and roll rod are minimizing the sample production time. Available printing widths are 165 / 185 / 225 / 250 / 285 / 330 cm. Effective printing lengths are 9.5 / 11.5 / 13.7 / 15.9 / 18.9 / 20.3. / 22.4 / 24.6 / 26.8 / 29 / 32 meters.

The Original Zimmer Magnet System Plus is the most efficient system for magnetic roll rod printing in warp direction. According to the requirements of the textile product, the magnet bars are available as standard magnet bars MB 38/40, or optionally with stronger magnet power SMP 70/55 (e. q. for towel printing).



SAMPLING & LAB MACHINES






2 | Magnetic Single Roll Rod can be chosen in various different diameters from 6 to 50 mms. Repeat adjustment may vary from 60 to **350 cms.** The magnet bar carriage is equipped with an individual servo drive with stepless speed adjustment.



Switch cabinet

Touch screen panel for pre selection of repeat sizes yardage, glueing, printing and washing processes.



ZIMMER AUSTRIA | SCREEN & COATING SYSTEMS

SAMPLING & LAB MACHINES

The Midi-II-R - rotary screen printing system

The Midi-II-R sample printing machine can optionally be equipped with different printing heads which are usually the same as your Rotascreen production machine.

Available printing widths are 165 / 185 / 225 / 250 / 285 / 330 cm.

Effective printing lengths are 9.5 / 11.5 / 13.7 / 15.9 / 18.9 / 20.3. / 22.4 / 24.6 / 26.8 / 29 / 32 meters.





3 | Closed bearing printing head

type G with individual width ad-

justment of both printing heads

and automatic pre-repeat ad-


justment.





4 | RSDM-V open bearing printing head with colour trough.

5 | Open bearing printing head type U for fast handling during changing of the screens together with the roll rods.



autumn 2015 autumn 2015 autumn 2015 www.zimmer-austria.com www.zimmer-austria.com www.zimmer-austria.com